


Cat. No.	Packaging	Highlights	Applications								Specifications						ADHESIVE CHARACTERISTICS					COMPATIBILITIES			Dimensions without tab (mm)		
			PCR	qPCR	Short term storage / incubation / ELISA	Long-term storage	Cell culture and microbiology	Crystallography	HPLC	Fluorescence / luminescence	Sonication	Sterile	DNase RNase free	Chemical resistance	Drillable	Optically clear	Transparent	Opaque	Gas permeable	Material	Operating temperature	Type of adhesive	Film thickness (µm)	Adhesive thickness (µm)		Two-component plate	8-tube bar and plate column
760212	Sheet	Does not withdraw into itself	•			•						•	•	•			•	Aluminium	-80 °C to +120 °C	Acrylic	35.6	27.9	•		Skirt and half-skirt	Without collar	125,4 x 82,6
760213	Sheet	Does not withdraw into itself	•			•						•	•	•			•	Aluminium	-80 °C to +120 °C	Acrylic	35.6	27.9	•		Skirt and half-skirt	Without collar	125,4 x 82,6
760231	Sheet	Reinforced sealing for 96-well plates	•			•						•	•				•	Aluminium	-80 °C to +120 °C	Acrylic	38.1	37.6			All types of skirts	With collar	117,5 x 77,8
760232	Sheet	Reinforced sealing for 384-well plates	•			•						•	•				•	Aluminium	-80 °C to +120 °C	Acrylic	38.1	37.6			Skirt and half-skirt	Without collar	123,8 x 82,6
760206	Sheet	Easy to remove	•			•						•	•		•			Polypropylene	-40 °C to +120 °C	Acrylic	50.8	24.1			Skirt and half-skirt	Without collar	123,1 x 79,4
760207	Sheet	Easy to remove	•			•						•	•		•			Polypropylene	-40 °C to +120 °C	Acrylic	50.8	24.1			Skirt and half-skirt	Without collar	123,1 x 79,4
765267	Sheet	Superior adhesion minimising evaporation	•									•			•			Polyester	-20 °C to +120 °C	Acrylic	50.8	41.9			All types of skirts	With or without collar	118,1 x 78,3
765276	Sheet	Superior adhesion minimising evaporation	•									•			•			Polyester	-20 °C to +120 °C	Acrylic	50.8	41.9			Skirt and half-skirt	Without collar	121,9 x 81,5
760229	Sheet	Superior adhesion minimising evaporation	•									•			•			Polyester	-40 °C to +120 °C	Acrylic	50.8	41.9			All types of skirts	With collar	118,1 x 78,3
765264	Sheet	Superior adhesion minimising evaporation	•									•			•			Polyester	-40 °C to +120 °C	Acrylic	50.8	41.9			Skirt and half-skirt	Without collar	125,1 x 79,4
765269	Sheet	Scored sheet per column of 8 wells	•									•			•			Polypropylene	-20 °C to +120 °C	Acrylic	50.8	41.9	•		Skirt and half-skirt	Without collar	73,3 x 10,1
760248	Sheet	Scored sheet in 2 columns of 8 wells	•									•			•			Polyester	-40 °C to +120 °C	Acrylic	50.8	26.7			Skirt and half-skirt	With collar	76,2 x 19,1
765282	Sheet	Opaque	•									•			•			Aluminium	-20 °C to +120 °C	Acrylic	50.8	36.8			All types of skirts	With or without collar	118,1 x 78,3
765281	Sheet	Opaque	•									•	•		•			Aluminium	-20 °C to +120 °C	Acrylic	50.8	36.8			All types of skirts	With or without collar	118,1 x 78,3
765268	Sheet	Scored sheet per column of 8 wells	•									•	•		•			Aluminium	-20 °C to +120 °C	Acrylic	50.8	36.8	•		Skirt and half-skirt	Without collar	81,2 x 10,1
765270	Roll	Excellent chemical resistance	•									•	•		•			Aluminium	-20 °C to +120 °C	Acrylic	50.8	36.8			All types of skirts	With or without collar	117,1 x 78,3
765246	Sheet	Silicone adhesive is released only when pressure is applied for a perfect adhesion without interference with the sample	•	•		•		•	•			•	•		•			Polyolefin	-80°C to +105°C	Silicone	50.8	50.8			All types of skirts	With or without collar	116,2 x 78,3
765265	Sheet	Silicone adhesive is released only when pressure is applied for a perfect adhesion without interference with the sample	•	•		•		•	•			•	•		•			Polyolefin	-80°C to +105°C	Silicone	50.8	50.8			All types of skirts	With or without collar	116,2 x 78,3
760236	Sheet	High optical quality films with excellent adhesion	•	•								•			•			Polyester	-40 °C to +120 °C	Acrylic	50.8	29.2	•		All types of skirts	With or without collar	118,1 x 77,8
760208	Sheet	High optical quality films with excellent adhesion	•	•								•			•			Polyester	-40 °C to +120 °C	Acrylic	50.8	29.2	•		Skirt and half-skirt	Without collar	121,9 x 79,4
765272	Roll	Minimises evaporation, available with colour spotlight				•									•			Polyester	-40 °C to +120 °C	Acrylic	50.8	26.7			Skirt and half-skirt	Without collar	121,9 x 79,4
765273	Sheet	Scored sheet per column of 8 wells				•						•			•			Polyester	-40 °C to +120 °C	Acrylic	50.8	26.7	•		Skirt and half-skirt	Without collar	82,6 x 9,5
765274	Sheet	Scored sheet per column of 8 wells				•						•			•			Polyester	-40 °C to +120 °C	Acrylic	50.8	26.7	•		Skirt and half-skirt	Without collar	82,6 x 9,5
760202	Sheet	Scored sheet in 2 columns of 8 wells				•						•			•			Polypropylene	-40 °C to +120 °C	Acrylic	50.8	26.7	•		Skirt and half-skirt	Without collar	82,6 x 19,1
760203	Sheet	Scored sheet in 2 columns of 8 wells				•						•			•			Polypropylene	-40 °C to +120 °C	Acrylic	50.8	26.7	•		Skirt and half-skirt	Without collar	82,6 x 19,1
760227	Sheet	Minimises evaporation, available with colour spotlight (assortments)				•									•			Polyester	-40 °C to +120 °C	Acrylic	50.8	26.7			Skirt and half-skirt	Without collar	125 x 79,4
760226	Sheet	Minimises evaporation, available with colour spotlight (blue)				•									•			Polyester	-40 °C to +120 °C	Acrylic	50.8	26.7			Skirt and half-skirt	Without collar	125 x 79,4
760222	Sheet	Minimises evaporation, available with colour spotlight (green)				•									•			Polyester	-40 °C to +120 °C	Acrylic	50.8	26.7			Skirt and half-skirt	Without collar	125 x 79,4



Cat. No.	Packaging	Highlights	Applications								Specifications							CHARACTERISTICS OF THE ADHESIVE					Dimensions without tab (mm)			
			PCR	qPCR	Short term storage / incubation / ELISA	Long-term storage	Crystallography	HPLC	Fluorescence / luminescence	Sonication	Sterile	DNase RNase free	Chemical resistance	Drillable	Optically clear	Transparent	Opaque	Gas permeable	Material	Operating temperature	Type of adhesive	Film thickness (µm)		Adhesive thickness (µm)	Two-component plate	8-tube bar and plate column
760223	Sheet	Minimises evaporation, available with colour spot (lavender)			•									•			Polyester	-40 °C to +120 °C	Acrylic	50.8	26.7			Skirt and half-skirt	Without collar	125 x 79,4
760224	Sheet	Minimises evaporation, available with colour spotlight (orange)			•									•			Polyester	-40 °C to +120 °C	Acrylic	50.8	26.7			Skirt and half-skirt	Without collar	125 x 79,4
760225	Sheet	Minimises evaporation, available with colour spotlight (red)			•									•			Polyester	-40 °C to +120 °C	Acrylic	50.8	26.7			Skirt and half-skirt	Without collar	125 x 79,4
765283	Sheet	Good sealing			•									•		•	Polypropylene	-40 °C to +120 °C	Acrylic	50.8	25.4			Skirt and half-skirt	Without collar	125 x 79,4
765277	Sheet	Good sealing			•									•		•	Polypropylene	-40 °C to +120 °C	Acrylic	50.8	25.4			Skirt and half-skirt	Without collar	125 x 79,4
765278	Sheet	Economy version			•									•			Polyester	-40 °C to +120 °C	Acrylic	50.8	26.7			Skirt and half-skirt	Without collar	123,4 x 79,4
765252	Roll	Minimises evaporation, available with colour spotlight			•									•			Polyester	-40 °C to +120 °C	Acrylic	38.1	26.7			Skirt and half-skirt	Without collar	120,7 x 79,4
765254	Roll	Minimises evaporation, available with colour spotlight			•									•			Polyester	-40 °C to +120 °C	Acrylic	38.1	26.7			Skirt and half-skirt	Without collar	120,7 x 79,4
765253	Roll	Minimises evaporation, available with colour spotlight			•									•			Polyester	-40 °C to +120 °C	Acrylic	38.1	26.7			Skirt and half-skirt	Without collar	120,7 x 79,4
765255	Roll	Minimises evaporation, available with colour spotlight			•									•			Polyester	-40 °C to +120 °C	Acrylic	38.1	26.7			Skirt and half-skirt	Without collar	120,7 x 79,4
760200	Sheet	Minimises evaporation, available with colour spotlight			•									•			Polyester	-40 °C to +120 °C	Acrylic	50.8	26.7			Skirt and half-skirt	Without collar	125,1 x 79,4
760201	Sheet	Minimises evaporation, available with colour spotlight			•									•			Polyester	-40 °C to +120 °C	Acrylic	50.8	26.7			Skirt and half-skirt	Without collar	125,1 x 79,4
760205	Sheet	Thin film easily pierced with a pipette tip			•									•		•	Polyester	-40 °C to +120 °C	Acrylic	25.4	24.1			Skirt and half-skirt	Without collar	121,2 x 79,4
760204	Sheet	Thin film easily pierced with a pipette tip			•									•		•	Polyester	-40 °C to +120 °C	Acrylic	25.4	24.1			Skirt and half-skirt	Without collar	121,2 x 79,4
765266	Sheet	Excellent chemical resistance				•										•	Aluminium	-80 °C to +120 °C	Acrylic	48.3	30.5			All types of skirts	With or without collar	118,1 x 78,3
765256	Roll	Gas permeable														•	Rayon	-20 °C to +80 °C	Acrylic	139.7	-			Skirt and half-skirt	Without collar	120,7 x 82,6
765258	Roll	Gas permeable														•	Rayon	-20 °C to +80 °C	Acrylic	139.7	-			Skirt and half-skirt	Without collar	120,7 x 82,6
765257	Roll	Gas permeable														•	Rayon	-20 °C to +80 °C	Acrylic	139.7	-			Skirt and half-skirt	Without collar	120,7 x 82,6
765259	Roll	Gas permeable														•	Rayon	-20 °C to +80 °C	Acrylic	139.7	-			Skirt and half-skirt	Without collar	120,7 x 82,6
760234	Sheet	After sampling and removal of the tip, the "X" closes and the sample is still protected from contamination															Vinyl	-40 °C to +90 °C	Acrylic	88.9	17.8			Skirt and half-skirt	Without collar	124,5 x 79,4
760235	Sheet	After sampling and removal of the tip, the "X" closes and the sample is still protected from contamination															Vinyl	-40 °C to +90 °C	Acrylic	88.9	17.8			Skirt and half-skirt	Without collar	124,5 x 79,4
760216	Sheet	Ideal for robotic systems															Polyethylene	-40 °C to +90 °C	Acrylic	70	25			Skirt and half-skirt	Without collar	142,9 x 82,6
760247	Sheet	Ideal for robotic systems															Polyethylene	-40 °C to +90 °C	Acrylic	70	25			Skirt and half-skirt	Without collar	142,9 x 82,6
760220	Sheet	No adhesive in front of the wells, ideal for use with tips and in robotics															Polyethylene	-40 °C to +90 °C	Acrylic	69.9	26.7			Skirt and half-skirt	Without collar	121,9 x 79,4
760241	Sheet	Absorbs light, reduces stray light															Vinyl	-40 °C to +80 °C	Acrylic	203.2	36.8			Skirt and half-skirt	Without collar	114,3 x 76,2
760245	Sheet	Reflects light and increases sensitivity															Vinyl	-40 °C to +80 °C	Acrylic	203.2	36.8			Skirt and half-skirt	Without collar	116,1 x 76,2
760214	Sheet	Gas permeable															Rayon	-20 °C to +80 °C	Acrylic	139.7	-			Skirt and half-skirt	Without collar	127 x 82,6
760215	Sheet	Gas permeable															Rayon	-20 °C to +80 °C	Acrylic	139.7	-			Skirt and half-skirt	Without collar	127 x 82,6